

**Product Details for 1 -1337417 -0**

**N Series RF Connectors**

[RoHS Compliant](#) (Statement of Compliance)

**Product Highlights:**

- ? Connector
- ? Jack Receptacle
- ? Coaxial Cable Termination Type = Solder
- ? Terminate To Wire
- ? Body Style = Straight

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

No Image Available

**1 -1337417 -0**

 [Active](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [TYPE-N BULKHEAD SOCKET FRONT MOUNT 50 OHM](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? Gender = Jack Receptacle
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? Lightning/EMP Protection = None
- ? [Dielectric Material](#) = PTFE
- ? Weatherproof = No
- ? Flats Dimension = 19.0 A/F
- ? Panel Thickness (mm [in]) = 3.00 [0.118]
- ? Body Material = Brass
- ? Solder Terminal = With

**Mechanical Attachment:**

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Bulkhead, Hex Nut
- ? [Panel Attachment Style](#) = Front Mount
- ? Panel Cutout = 15.9mm x 14.6mm Double D Shape
- ? Flange Dimension [Dia.] (mm [in]) = 19 [0.748]
- ? Flange and Thread Material = Brass
- ? Lockwasher Material = Brass
- ? Lockwasher Plating = Silver

**Electrical Characteristics:**

- ? Frequency = DC - 11 GHz
- ? Connector Impedance (?) = 50

**Termination Related Features:**

- ? Coaxial Cable Termination Type = Solder

**Body Related Features:**

- ? [Body Plating](#) = Silver

**Contact Related Features:**

- ? [Center Contact Plating](#) = Silver
- ? Center Contact Material = Brass

**Housing Related Features:**

- ? Captured Center Contact = With

**Industry Standards:**

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

**Conditions for Usage:**

- ? Terminate To = Wire
- ? Operating Temperature (Max.) (°C) = 165

**Packaging Related Features:**

- ? Packaging Method = Individual
- ? Packaging Quantity = 50

**Other:**

- ? Brand = Greenpar