


Product Details for 1 -1337466 -0



1 -1337466 -0

[Active](#)

TNC RF Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Plug
- ? Terminate To Coaxial Cable
- ? Coaxial Cable Termination Type = MIL -Clamp
- ? Coaxial Cable Type (RG/U or Mfg.) = 141A/U, 58C/U, Raychem 5019D3318, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 60470Q, Raychem EPD 64319Q, Raychem EPD 71169Q, URM 43, URM 76

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [TNC STRAIGHT PLUG SOLDER MIL -CLAMP 50 OHM RG58C/U, 1...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Plug
- ? [Body Style](#) = Straight
- ? [Body Material](#) = Brass
- ? Weatherproof = No
- ? [Solder Terminal](#) = Without
- ? Grade = Professional
- ? Flats Dimension = 9.5 A/F
- ? Dielectric Material = PTFE
- ? Coupling Nut Material = Brass
- ? Gasket Material = White Silicone Rubber
- ? Safety Wire Holes = Without

Mechanical Attachment:

- ? Panel Attachment = Without

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Frequency = DC - 11 GHz

Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = MIL -Clamp

Body Related Features:

- ? [Body Plating](#) = Silver

Contact Related Features:

- ? Center Contact Plating = Silver
- ? Center Contact Material = Brass

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 141A/U, 58C/U, Raychem 5019D3318, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 60470Q, Raychem EPD 64319Q, Raychem EPD 71169Q, URM 43, URM 76

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable
- ? Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- ? Packaging Method = Individual
- ? Packaging Quantity = 50

Other:

- ? Brand = Greenpar