| typeElectronicsProductsDocumentation | Resources My Account Customer S | | Sign In In Text Tips Mber | |
|--|--|---|--|--|
| Home > Products > By Type > Circular Industrial > Product Feature Selector > Product Details | | | | |
| Product Details for 182 | | | | |
| No Image Available | CPC Accessories RoHS Compliant (Statement of C Product Highlights: ? Cable Clamp | Compliance) | Quick Links <u>Check Pricing &</u> <u>Availability</u> <u>Search for Tooling</u> <u>Product Feature</u> <u>Salacter</u> | |
| 182928 -1 | Shell Size = 11 Body Style = Straight Cable Diameter (Max.) = 11.5 Thermoplastic Cable Clamp N <u>View all Features</u> | | Selector Contact Us About This Product | |
| Documentation & Addition | onal Information | | | |
| Product Drawings: CPC cable clamp kit Catalog Pages/Data Shee None Available Product Specifications: None Available Application Specification None Available Instruction Sheets: None Available CAD Files: None Available | NS: | Additional P ? Product ? Product | Ct Line Information Product Images: Ct Usage Ct Usage Ct Usage Ct Usage Ct Usage Ct Usage | |
| Product Features (Please Product Type Features: ? Product Type = Ca ? Shell Size = 11 ? Body Style = Straig ? Thread Size = 5/8 Body Related Features: | ght | Industry Standards: ? RoHS/ELV Compliance compliant ? Lead Free Solder Process lead free process ? RoHS/ELV Compliance H comply with RoHS directive | ses = Not relevant for istory = Converted to | |

? <u>Cable Diameter (Max.) (mm [in])</u> = 11.51

Packaging Related Features:

[0.453]

- ? <u>Cable Clamp Material</u> = Thermoplastic
- ? <u>Cover</u> = Without
- Cable Clamp Flammability Rating = UL94V -1

<u>Packaging Method</u> = Individual
 Packaging Quantity = 50
 Other:

 Brand = AMP

Languages : English | Deutsch | Español | Português (do Brasil) | ??????? | Italiano | ???? (??) | ?? (??) | ??? Country Sites : China | Japan

> © 2006 Tyco Electronics Corporation All Rights Reserved Home | Customer Support | Supplier | Site Map | Privacy Policy | Browser Support