




PRODUCT CATALOG

 English 日本語
Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Terminals and Splices
↳ Ring and Spade Tongue Terminals
AMP **2-34853-1**  [Active](#)
**Directive 2002/95/EC
Compliant**
[RoHS Compliant](#)
(Tyco Electronics P/N: 2-34853-1)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> » General Info » Sales Info » Assembly Subcontractors 	<ul style="list-style-type: none"> » Pricing » Product Availability 	<ul style="list-style-type: none"> » Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
Searchable Features:

Brand:	AMP
Government/Industry Qualification:	No
Terminal Shape:	Ring Tongue
Receptacle Style:	Straight
Body Style:	PLASTI-GRIP
Barrel Type:	Closed Barrel
Wire/Cable Type:	Regular Wire
Wire Range (mm [AWG]):	2.62-6.64 ² [12-10]
Wire Range (CMA):	5,180 – 13,100
Insulation:	Yes

Other Properties:

Voltage (VAC):	600
Tongue Material Thickness (mm [in]):	1.07 [0.042]
Color:	Yellow
Insulation Material:	Vinyl
Packaging Quantity:	2,500

Insulation Support:	Insulation Support
Insulation Diameter (mm [in]):	6.35 [.250] Max.
Stud Size:	8 [M4]
Stud Diameter (mm [in]):	4.17 [0.164]
Shape:	RING-043
Heavy Duty:	Standard
Packaging Method:	Tape Mounted
Material:	Copper
Finish:	Tin

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)