

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

AMPMODU

 **.100 Centerline Receptacles (HV-100 and HV-190)**
AMP 216602-8  [Active](#) [Not Reviewed for ELV/RoHS Compliance](#)
**(Tyco Electronics P/N:
216602-8)**
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▶ General Info ▶ Sales Info ▶ Assembly Subcontractors 	<ul style="list-style-type: none"> ▶ Pricing ▶ Product Availability 	<ul style="list-style-type: none"> ▶ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[PCB Layout](#)
Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not reviewed for compliance
Product Type:	HV-190
No. of Rows:	Single
No. of Positions:	8
Contact Mating Area Plating:	Gold (30)
Connector Height (mm [in]):	3.20 [0.126]
Housing Entry Style:	Side
Sealed:	No
Mount Angle:	Right Angle

Other Properties:

Housing Material:	Polyester GV
Color:	Green
Housing Material Flammability Rating:	UL 94V-0
Contact Material:	Phosphor Bronze
Terminate To:	Printed Circuit Board
Centerline (mm [in]):	2.54 [0.100]
Solder Tail Plating:	Tin
Packaging Quantity:	105

PCB Retention Feature:	No
Stackable:	End by End
Closed Bottom:	No
Termination Post Length (mm [in]):	3.20 [0.126]
Termination Method:	Through Hole

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)