




[English](#)   [日本語](#)

## Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

## Subminiature and Microminiature D Connectors

### ↳ Subminiature D Pin/Socket Connectors for MIL-C-24308 and MIL-C-39029

**AMP**   **206793-1 (G-10-S1)**      [Active](#)

**Directive 2002/95/EC  
Compliant**

[RoHS Compliant](#)

(Tyco Electronics P/N: 206793-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>▶ <a href="#">General Info</a></li> <li>▶ <a href="#">Sales Info</a></li> <li>▶ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>▶ <a href="#">Pricing</a></li> <li>▶ <a href="#">Product Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>▶ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
<b>Brand:</b>	AMP
<b>Government/Industry Qualification:</b>	Yes
<b>Government/Industry Part Number:</b>	G-10-S1
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Process:</b>	Not relevant for lead free process
<b>Product Type:</b>	Contact
<b>Product Series:</b>	109
<b>Terminate To:</b>	Wire

Other Properties:	
<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>High Current:</b>	No
<b>Contact Material:</b>	Copper Alloy
<b>Contact Mating Area Plating:</b>	Gold

<b>Gender:</b>	Socket
<b>Contact Size:</b>	20
<b>Wire Termination Type:</b>	Crimp
<b>Contact Style:</b>	Crimp Snap-in
<b>Packaging Method:</b>	Loose Piece
<b>Post Diameter (mm [in]):</b>	1.75 [0.069]
<b>Wire Range (mm [AWG]):</b>	0.60-0.20 <sup>2</sup> [20-24]
<b>Insulation Diameter (mm [in]):</b>	1.83 [.072] Max.

---

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)