


## 390261-8 Product Details

[Live Product Chat](#)


390261-8

### DIP Sockets

Not EU RoHS or ELV Compliant ([Find RoHS Compliant Alternates](#))

#### Product Highlights:

- DIP Socket
- 24 Positions
- Row-to-Row Spacing = 7.62 mm
- Through Hole Contact Termination Type
- Mount Style = Vertical

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

TE Internal Number: 390261-8



**Superseded**

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

[Search for Replacement Parts](#)

### Documentation & Additional Information

#### Product Drawings:

- [DIP SOCKET, .300 CENTER LINE LADDER STYLE \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = DIP Socket
- [Number of Positions](#) = 24
- Profile = Standard
- [Frame Style](#) = Ladder
- [Leg Style](#) = Straight
- PCB Mount Angle = Horizontal

#### Electrical Characteristics:

- Insulation Resistance (MΩ) = 10,000
- Contact Resistance (mΩ) = 30

#### Termination Related Features:

- [Termination Post Length \(mm \[in\]\)](#) = 3.00 [0.118]

#### Body Related Features:

- [Row-to-Row Spacing \(mm \[in\]\)](#) = 7.62 [0.300]
- [Mount Style](#) = Vertical
- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

#### Contact Related Features:

- [Contact Termination Type](#) = Through Hole
- [Contact Base Material](#) = Phosphor Bronze
- [Contact Plating, Mating Area, Material](#) = Tin-Lead
- [Contact Style](#) = Stamped + Formed
- [Mating Contact Type](#) = Dual Leaf

#### Configuration Related Features:

- [Height Above PC Board \(mm \[in\]\)](#) = 5.10 [0.200]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

#### Conditions for Usage:

- Temperature Range (°C) = -40 - +105

#### Packaging Related Features:

- [Packaging Method](#) = Tube

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)