

Product Details for 487769 - 2



487769 - 2

[Active](#)

Flexible Film Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? [Housing](#)
- ? [2.54 mm Centerline](#)
- ? [Connector Type = Slimline](#)
- ? [Number of Positions = 4](#)
- ? [Number of Rows = Single](#)

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(12\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

CAD Files:

- ? [None Available](#)

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Typical Application](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(12\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Housing
- ? [Connector Type](#) = Slimline
- ? [Number of Positions](#) = 4
- ? [Mating Type](#) = Receptacle
- ? [Mating Connector Lock](#) = With
- ? [Mating Connector Lock Type](#) = Detent
- ? [Mating Polarization](#) = Without
- ? [Mounting Ears](#) = Without
- ? [Flame Retardant](#) = Yes

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Number of Rows](#) = Single

Housing Related Features:

- ? [Housing Material](#) = Thermoplastic
- ? [Housing Flammability Rating](#) = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = FFC Cable

Other:

- ? [Brand](#) = AMP