


**Product Details for 5223016 -4**



**5223016 -4**

[Active](#)

**2mm Centerline Futurebus+ Connectors**

[RoHS Compliant](#) (Statement of Compliance)

**Product Highlights:**

- ? Module Type = Signal
- ? 120 Signal Positions
- ? Fixed -Board (Header)
- ? Mating Post Length = 5.75 mm
- ? PCB Mount Angle = Vertical

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(12\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [ASSEMBLY, PIN, SIGNAL, VERTICAL, Z -PACK 2mm FB, 5 RO...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? [Connector, Z -PACK\\*, 2 mm FB, Signal and Power](#) (PDF, English)

**Application Specifications:**

- ? [Z-PACK 2mm FB \(Futurebus+\) Receptacle and Pin Header...](#) (PDF, English)

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)
- ? [Mating Products \(12\)](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Fixed -Board (Header)
- ? [PCB Mount Angle](#) = Vertical
- ? [Post Type](#) = Press -Fit
- ? Comment = Sequencing of the mating posts and lead lengths is available. Worksheets for this procedure may be found under Z -PACK 2mm FB General Information.

**Mechanical Attachment:**

- ? [Module Type](#) = Signal
- ? [Mating Post Length \(mm \[in\]\)](#) = 5.75 [0.226]
- ? Press -Fit Post Style = Compliant Pin
- ? Pin Header Width (mm [in]) = 18.00 [0.709]

**Electrical Characteristics:**

- ? Voltage Rating (VAC) = 30

**Termination Related Features:**

- ? [Termination Post Length \(mm \[in\]\)](#) = 4.25 [0.167]

**Body Related Features:**

- ? [Number of Signal Positions](#) = 120
- ? [Sequencing](#) = No
- ? [Number of Rows](#) = 5
- ? [Post Plating](#) = Tin
- ? Centerline, Matrix (mm [in]) = 2.00 x 2.00 [0.079 x 0.079]

**Contact Related Features:**

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating = Gold (30)

**Housing Related Features:**

- ? Housing Material = Liquid Crystal Polymer (LCP)

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Other:**

- ? Brand = AMP