
Home > Products > Product Feature Selector > Product Details

# 1-322249-0 Product Details





1-322249-0

Ring and Spade Tongue Terminals

# Always EU RoHS/ELV Compliant (Statement of Compliance)

- Product Highlights: Terminal Shape = Spade Tongue, Flanged

- Receptacle Style = Straight Body Style = PLASTI-GRIP Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

View all Features



### Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

TE Internal Number: 1-322249-0

🔁 View 3D PDF









#### Documentation & Additional Information

#### Product Drawings:

TERMINAL, SPADE, FLANGED, PLASTI-GRIP, WIRE SIZE: 22... (PDF, English)

#### Catalog Pages/Data Sheets:

## Product Specifications:

### Application Specifications:

PLASTI-GRIP Terminals and Splices (PDF, English)

#### Instruction Sheets:

## CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version L)
- 3D Model (IGES, Version L)
- 3D Model (STEP, Version L)

#### **Additional Information:**

Product Line Information

#### Additional Product Images:

Product Photo

#### Related Products:

Tooling

List all Documents

## Product Features (Please use the Product Drawing for all design activity)

## Product Type Features:

- <u>Terminal Shape</u> = Spade Tongue, Flanged
- <u>Receptacle Style</u> = Straight Body Style = PLASTI-GRIP
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire
- Insulation = Yes
- Insulation Support = Insulation Support
- Insulation Diameter (mm [in]) = 2.67-3.56 [.105-.140]
- Stud Diameter (mm [in]) = 4.34 [0.171]
- Stud Size = 8 [M4]
- Shape = SPADE-025
- Heavy Duty = No
- <u>Material</u> = Copper
- $\underline{\mathsf{Finish}} = \mathsf{Tin}$
- Tongue Material Thickness (mm [in]) = 0.79 [0.031]
- Color = Red
- Insulation Material = Vinyl

# **Electrical Characteristics:**

Voltage (VAC) = 600

### **Body Related Features:**

- Wire Range (mm [AWG]) = 0.30-1.402 [22-16]
- Wire Range (CMA) = 509 3,260

### **Industry Standards:**

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- <u>Lead Free Solder Processes</u> = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant

## Packaging Related Features:

- Packaging Method = Loose Piece
- Packaging Quantity = 1,000

## Other:

Brand = AMP



Corporate Information

Who We Are Investors News Room Supplier Portal

Careers

Quick Links

Check Distributor Inventory

Cross Reference

Find Documents & Drawings

Product Compliance Support Center

Site Map

**Customer Support** 

Email or Chat with Us Find a Phone Number Search Knowledge Base Manage Your Account

Sign up for our eNewsletter

Enter your email address













