

## 280050-7 Product Details


Have a Question?

Chat with a Product Information Specialist



280050-7

TE Internal Number: 280050-7

 Active

 [View 3D PDF](#)

### FASTON Uninsulated Receptacles & Housings

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)


#### Product Highlights:

- Product Classification = Connectors - Terminals and Splices
- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Board Mount = No

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [.250 srs. flag faston rec.](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Blocchetto di protezione per capicorda lamellari fem...](#) (PDF, Italian)

#### Application Specifications:

- [FASTON & FASTIN-FASTON conn. .250 srs. flag rec. etc.](#) (PDF, Italian)

#### Instruction Sheets:

- None Available

#### CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version BD)
- [3D Model](#) (IGES, Version BD)
- [3D Model](#) (STEP, Version BD)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Classification = Connectors - Terminals and Splices
- Product Type = Terminal
- [Terminal Type](#) = Receptacle
- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 x 0.81 [.250 x .032]
- [Receptacle Style](#) = Flag
- [Insulation Support](#) = Insulation Support
- [Wire/Cable Type](#) = Stranded
- [Insulation Diameter \(mm \[in\]\)](#) = 2.36-3.30 [.093-.130]
- [Insertion Force](#) = Normal
- [Material](#) = Phosphor Bronze
- [Finish](#) = Tin
- [Crimp Type](#) = F-Crimp
- Comment = Versions according DIN 46345

#### Mechanical Attachment:

- [Board Mount](#) = No

#### Body Related Features:

- [Weld Tab](#) = Without
- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.50<sup>2</sup> [20-15]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Reverse Reeled

#### Other:

- [For Hermetic Header Tab](#) = No
- [Line](#) = Premier
- Brand = AMP

 BOOKMARK 

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

#### Follow Us On:



Visit Us On:

