

499923-8 Product Details

Have a Question?

Chat with a Product Information Specialist



499923-8

TE Internal Number: 499923-8

Active

[View 3D PDF](#)

Pin and Pinless Headers (AMP-LATCH)

[5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

Product Highlights:

- Preloaded
- Connector Style = Header - Pin
- Header Type = Universal Ejection Pin Headers
- AMP-LATCH Product Line
- Standard Profile

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [HEADER ASSY, UNIVERSAL, AMP-LATCH](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [AMP-LATCH* and IDC Header Connectors, .100 x .100 In...](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- [AMP* INSTALLATION PROCEDURES FOR AMP-LATCH* UNIVERSA...](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version G)
- [3D Model](#) (IGES, Version G)
- [3D Model](#) (STEP, Version G)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = AMP-LATCH
- Profile = Standard
- PCB Mount Angle = Vertical
- PCB Mount Retention = Without
- Mating Polarization Type = Center, Dual Polarizing Bar, Military
- Mating Connector Lock = With
- Housing Style = 4-Sided
- Ejection Latches = With
- Post Size (mm [in]) = 0.64 [.025]
- Shrouded = Yes
- Mating Polarization = With
- Latch Type = Long
- Mating Connector Lock Type = Latch

Termination Related Features:

- Termination Post Length (mm [in]) = 3.94 [0.155]
- Solder Tail Contact Plating = Tin-Lead

Body Related Features:

- Header Type = Universal Ejection Pin Headers
- Number of Positions = 34
- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

Contact Related Features:

- Preloaded = Yes
- Contact Plating, Mating Area, Material = Gold (15)
- Contact Shape = Square

Housing Related Features:

- Connector Style = Header - Pin
- Housing Material = Thermoplastic - GF
- UL Flammability Rating = UL 94V-0
- Housing Color = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Conditions for Usage:

- Temperature Rating = Standard
- PCB Thickness, Recommended (mm [in]) = 3.18 [0.125]

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

