

5-1634556-0 Product Details

Have a Question?

Chat with a Product Information Specialist



5-1634556-0

BNC RF Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Printed Circuit Board
- Body Style = Elbow

[View all Features](#)

TE Internal Number: 5-1634556-0

[Active](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [BNC LP ELBOW BULKHEAD PCB SKT 50 & 75 OHMS \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- Gender = Jack
- Body Style = Elbow
- [PCB Mount Angle](#) = Right Angle
- [Grade](#) = Professional
- [PCB Height \(mm \[in\]\)](#) = 10.94 [0.431]
- [PCB Mount Retention](#) = Without
- Mounting Post Style = Round
- [Mounting Post Length \(mm \[in\]\)](#) = 3.33 [0.131]
- [Body Material](#) = Zinc
- [Sealed](#) = No
- [Isolated](#) = No
- [Dielectric Material](#) = PTFE/TPX
- Number of Ports = 1

Mechanical Attachment:

- Surface Mountable = No
- [Panel Attachment](#) = With
- [Panel Attachment Method](#) = Bulkhead

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50
- Frequency = DC - 4 GHz

Body Related Features:

- [Hardware Included](#) = No
- [Body Plating](#) = Nickel
- [Polarized](#) = No

Contact Related Features:

- [Center Contact Material](#) = Phosphor Bronze
- [Center Contact Plating](#) = Gold

Housing Related Features:

- Connector Style = Jack

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Printed Circuit Board
- Operating Temperature (Max.) (°C) = 85

Packaging Related Features:

- Packaging Method = Individual
- Packaging Quantity = 50

Other:

- Brand = Tyco Electronics

BOOKMARK

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

