


88976-5 Product Details

Have a Question?

Chat with a Product Information Specialist



88976-5

TE Internal Number: 88976-5

Active

Flexible Film Contacts

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- IDC Termination Method to Wire/Cable
- Contact Type = Pin
- 2.54 mm Centerline
- Wire/Cable Type = Flexible Flat Conductor Cable

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CONTACT, FFC .100CL, .025 SQ PIN](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Connector, Flexible Flat Conductor Cable, .100 Inch ...](#) (PDF, English)
- [Connector, Flexible Flat Conductor Cable, .100 Inch ...](#) (PDF, Japanese)

Application Specifications:

- [Flexible Flat Cable \(FFC\) Housings with Contact Cavi...](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Contact
- [Termination Method to Wire/Cable](#) = IDC
- [Wire/Cable Type](#) = Flexible Flat Conductor Cable
- Comment = For use without housing.

Termination Related Features:

- Solder Tail Contact Plating = Gold Flash

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- [Conductor Width \(mm \[in\]\)](#) = 1.19 [0.047]

Contact Related Features:

- Contact Type = Pin
- [Contact Plating, Mating Area, Material](#) = Gold Flash over Palladium Nickel or Gold (15) over Nickel
- Contact Underplating = Nickel

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Strip

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

