



2102080-3 Product Details

[Share](#) [Print](#) [Email](#)


2102080-3

TE Internal Number: 2102080-3

 Active

 [View 3D PDF](#)

.050, .075, .100 Box Connectors

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Connector Style = Receptacle
- Connector Assembly
- Contact Type = Socket
- 1.27 mm Centerline
- Number of Rows = 6

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [ASSEMBLY, SOCKET, 60 POSITION, MINI-BOX STACKING CON...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [MEZALOK* Stacking Connector System](#) (PDF, English)

Application Specifications:

- [Mezalok Stacking Connectors](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Connector Type = Connector Assembly
- Sealed = No
- Strain Relief = Without
- [Mount Angle](#) = Vertical
- PCB Mount Style = Surface Mount - Solder Ball
- Color = Natural

Termination Features:

- Solder Ball Material = Tin Lead

Body Features:

- Centerline (mm [in]) = 1.27 [0.050]
- [Number of Rows](#) = 6
- [Number of Positions](#) = 60
- [Staggered Rows](#) = No
- Gasket = Without
- Pin Protection = Without
- Hybrid = No
- Jackscrews = Without
- Stabilizers = Without

Contact Features:

- Contact Type = Socket
- Contact Plating, Mating Area, Material = Gold (50)
- Contact Base Material = Beryllium Copper

Housing Features:

- Connector Style = Receptacle
- Housing Material = Liquid Crystal Polymer (LCP)

Configuration Features:

- Stack Height (mm [in]) = 12.00 [0.472]

Industry Standards:

- Government/Industry Qualification = No
- Industry Standard Configuration = None
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C

Operation/Application:

- Application = PC Solder Mount

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

