



Electronics

Shielded CHAMP Cable Connector Kits (Continued)


Inner Ferrule on Jacket


No. of Positions	Cable Diameter (Less Than)			
24	.300 7.62			
36	.350 8.89			
50	.400 10.16			

Inner Ferrule on Braid*

No. of Positions	Cable Diameter (Greater Than) .300 7.62 .350 8.89			
24				
36				
50	.400 10.16			

* Ferrule size based on braid bundle diameter.






No. of Positions	Cable Range	Part Numbers							
		Shielded Plug Kit				Shielded Receptacle Kit			
		Screw Lock		Bail Lock		Screw or Bail Lock		O Kit-	
		B Slot	E Slot	B Slot	E Slot	B Slot	E Slot	Cover Kits	
24	.250500 6.35-12.70	554948-4 ⁵ 554948-2 ⁴	554948-33	<u> </u>		_		554944-1	
36	.250500 6.35-12.70	554951-2	_	554950-2	554950-1		_	554945-1	
50	. 350625 8.89-15.88	554945-26	554954-1	554953-21	554953-11	554955-2	554955-1	554946-1 ² 554946-2	

¹ SCSI applicable.

Typical Cable Assembly (Shielding Effectiveness)



² For cable diameter of .500 [12.70] or less use -1 kit. For cable diameter greater than .500 [12.70] use -2 kit.

³ Connector with M3.5 threads kits includes M3.5 x 2.00 [50.80] standoff stud.

^{4 4-40} UNC-2B hole size.

⁵ M3.5 x 0.6-6G, shoulder stud screws (2) supplied.

⁶ Contact Tyco Electronics for RoHS Part Number information.