


BNC Connectors, 75 Ohm

Plugs, Crimp

These connectors have been designed for opt mum performance and have a true 75 ohm impedance the complete length of the connector. The crimp die tooling listed below is different from the equiva ent 50 ohm connectors.



Plugs

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu Head 318161-1	Part No.
179, 179A, 179B, 187, 187A, 161, Belden 9221	Hex Crimp	Gold	Nickel	Polyethelena	Commercial	29.46 1.160	58425-2	-	413589-8
	0 Crimp	Gold	Nickel	Polyethelens	Commercial	35.56 1.140	318451-2	-	221185-8
179	O Crimp	Gold	Nickel	Polyethelens	Economy	27.69 1.090	58559-1		414858-2
								_	414918-21
AT&T 735A	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2	_	1-413589-0
	O Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58174-1	58248-3	1-221185-8
AT&T KS 19224 L2, RD179 , Double Braid	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2	_	413589-4
Belden 8218	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2		413589-3
	0 Crimp	Gold	Nickel	Polyothelene	Commercial	27.69 1.090	58174 '	58248 3	221185-3
140, 210, 62, 62A, 62B, 59, 59A, 59B, Belden 9291, 9209, 9269	Hex Crimp	Gold	Vickel	Polyethelene	Commercial	29.46 1.160	58425-1	_	413589-2
	O Crimp	Gold	Vickel	Polyethelene	Commercial	27.69 1.090	58536-1	58248-2	221185-2
59. 59A, 59B	O Crimp	Gold	Vickel	Polyethelene	Economy	27.69 1.090	58558-1		414858-1
									414918-12
302, Belden 89269, 88241, Hi-Temp 62A, Times PL-62, Berk Tek BTDC-59, BTDC-62	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.45 1.160	58425-1	_	4 13589 -1
Belden 8212, 9104, 9112, 9167, 9240, 9259.	Hex Crimp	Gold	Vickel	Polyethelene	Commercial	29.46 1.160	58425-	_	413589-9
9266, Times FM-59, (RG-59 Type with 20 AWG C.C.)	O Crimp	Gold	Vickel	Polyethelene	Commercial	27.69 1.090	58536-	58248-2	221185-9
Belden 9145, AT&T /34A	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-1		413589-7
	O Crimp	Gold	Vickel	Polyethelene	Commercial	27.69 1.090	58536-	_	1-221185-0
Belden 9248, 9114	0 Crimp	Gold	Vickel	Polyethelene	Commercial	25.65 1.010	58536-1	=-	221185-1
6. 6A	O Crimp	Gold	Vickel	Polyethelene	Commercial	37.85 1.490	58538-^	58243-1	221185-7
Belden 8281, 9141, 9231.	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-3	_	413589-5
Western Electric 724. 728, 3049	O Crimp	Gold	Nickel	Polyethelene	Commercial	28.45 1.120	58538-1	58248 1	221185-5
Comm/Scope S59 Hec	O Crimp	Gold	Nickel	Polyethelene	Commercial	28.96	58536-1	_	2-221185-9
Comm/Scope F59 Hec-z	O Crimp	Gold	Vickel	Polyethelene	Commercial	28.96 1.140	58536-1	_	3-221185-1
Belden 88281	O Crimp	Gold	Vickel	Polyethelene	Commercial	27.69 1.090	58538-1		3-221185-3

'Kit includes connector subassembly and ferrule only, center contact part no. 1-414724-0 supplied separately on strip.

2Kit includes connector subassembly and ferrule only, center contact part no. 414724-4 supplied separately on strip.

3Terminate with Amp-o-lectric terminating machine 220152-1 with applicator.