

# Receptacle Housings

#### **Technical Features**

No. of Positions:

2 Positions

**Housing Material:** 

PBT GF15

Wire Size Range:


0.2-0.75 mm<sup>2</sup>

**Product Specification:** 

108-18272-0

**Application Specification:** 

114-18061



#### 2 Position Receptacle Housings

No. of Pos.	Keying Options	Housing Color	Part Numbers							
			Receptacle Housing	Cover	Locking Device	Cover and Lever	Retainer Housing	Mating Tab Housing	Mating PCI Right-Angle	B Header Vertical
	Α	Black	1-967644-1	_	_	_	_	_	=	_
2	В	Grey	2-967644-1							

### **Technical Features**

No. of Positions:

2 Positions

**Housing Material:** 

PA 66 GF

Wire Size Range:


 $0.35 - 0.75 \; mm^2$ 

**Product Specification:** 

108-20234

**Application Specification:** 

411-20066



## 2 Position Receptacle Housing

No. of Pos.	Keying Options	Housing Color	Part Numbers							
			Receptacle Housing	Cover	Locking Device	Cover and Lever	Retainer Housing	Mating Tab Housing	Mating PCI Right-Angle	3 Header Vertical
2	А	Black	284703-1	-	_	_	_	_	_	-