

BNC Connectors, 75 Ohm (Continued)

Right-Angle Plugs, Crimp

Connector Cable Range Selection Code†	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 678304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1
B1	179, 179A, 179B, 187, 187A, 161 Belden 9221	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-8	1.553 39.45	—	58425-2	—
B4	AT&T 735A	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	1-413588-0	1.553 39.43	—	58425-2	—
B5	AT&T KS 19224 L2, RD179 Double Braid	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-4	1.553 39.45	—	58425-2	—
C3	Belden 8218	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-3	1.553 39.45	—	58425-2	—
		Dual Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	221402-3	1.570 39.88	—	58174-1	58248-3
G	140, 210, 62, 62A, 62B, 59, 59A, 59B, Belden 9291, 9209, 9269	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-2	1.553 39.45	—	58425-1	—
		Dual Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	221402-2	1.570 39.88	—	58536-1	58248-2
G1	302, Belden 83241, 89269, Hi-Temp 62A, Times PL-62, Berk Tek BTDC-59, BIDC-52	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-1	1.553 39.45	—	58425-1	—
G3	Double Braided 59	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-6	1.553 39.45	—	58425-3	—
G4	Belden 8212, 9104, 9112, 9240, 9167, 9259, 9266, Times FM-59, (RG-59 Type with 20 AWG C.C.)	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-9	1.553 39.45	—	58425-1	—
		Dual Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	221402-4	1.570 39.88	—	58536-1	—
J1	Belden 9248, 9114	Dual Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	221402-1	1.570 39.88	—	58536-1	—
K2	Belden 8281, 914*, 9231, Western Electric 724, 728, 3049	Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-5	1.553 39.45	—	58425-3	—
		Hex Crimp	Gold	Nickel	Poly-methyl-pentene	Commercial	—	413588-5	1.553 39.45	—	58536-1	—

†Refer to pages 14 and 15 for code specifications.

BNC Connectors