

BNC Connectors, 75 Ohm (Continued)

Bulkhead Jacks, Crimp

Connector Cable Range Selection Code†	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 678304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1
B1	179, 179A, 179B, 161	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-8	1.450 36.83	—	58425-2	—
	187, 187A, Belden 9221	Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	221221-5	1.375 34.93	—	316451-2	—
B5	AT&T KS 19224 L2, RD179 Double Braid	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-4	1.450 36.83	—	58425-2	—
C3	Belden 8218	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-3	1.450 36.83	—	58425-2	—
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	221221-3	1.375 34.93	—	58174-1	58248-3
G	140, 211, 62, 62A, 62B, 59, 59A, 59B, Belden 9291, 9209, 9269	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-2	1.450 36.83	—	58425-1	—
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	221221-2	1.375 34.93	—	58536-1	58248-2
G1	302, Belden 88241, 89269, Hi-Temp 62A, Times PL-62, Berk Tex BTDC-59, BTDC 62	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-1	1.450 36.83	—	58425-1	—
G3	Double Shield RG-59	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-6	1.450 36.83	—	58425-3	—
G4	Belden 8212, 9104, 9112, 921C, 9167, 9256, 9266, Times FM-59 (RG-59 Type with 20 AWG C.C.)	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-9	1.450 36.83	—	58425-1	—
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	221221-7	1.375 34.93	—	58536-1	58248-2
G5	AT&T 734A Belden 9145	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-7	1.450 36.83	—	58425-1	—
J1	Belden 9114, 9248	Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	221221-1	1.375 34.93	—	58536-1	—
K2	Belden 8281, 9141, 9231 Western Electric 724, 728, 3049	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	413590-5	1.450 36.83	—	53425-3	—

†Refer to pages 14 and 15 for code specifications.

BNC Connectors