

REVISIONS				
DESCRIPTION	DATE	DWN	APVD	
017430	01AUG07	JR	TM	
″AMP 12–10*″, LOCATION X AS SHOWN.				D
E THICKNESS IS 1.0±0.05				
ES TO EDGE OF METAL WIRE L TO CENTER OF STUD HOLE,				
INSULATION DIA RANGE 3.81-6.35				
- COPPER PER ASTM B-152 E - PVC				
- TIN PL PER ASTM B-545 E - COLOR - YELLOW				
MAX OPERATING TEMPERATURE.				С
OLT MAX				
.64mm2 [5,180 - 13,1 DR STRANDED	00 CMA]]		
				В
LOOSE PIECE	130)677		
PACKAGE TYPE	PAR	T N()	
Electronics Corporation Harrisburg, PA 17105-3608				
TERMINAL RING TONGUE, PLASTI-GRIP, WIRE SIZE 12-10 -				А
ge code drawing no 0779 C =130677		RESTRIC	TED TO	
SCALE 4:1 SHE	EET 1 OF 1	REV	΄ Α	

1