

6[[2.400]	49.53[1.950]	125.73[4	L.950)] 105	.41[4.	150]	8	0	5822	021-5
3[2.200] 44.45[1.750]	115.57[4	1.550)] 95.	.25[3.750]		7	72 5822		021-4	
\square			С	B			A		NO POS	OF SN	PART NO	
CONTROLLED DOCUMENT.			DWN S.WAITMAN CHK M.YEOMANS	5JAN05	TE Connectivity							
		_	APVD M.YEOMANS PRODUCT SPEC —	5jano5 S	NAME CONNECTOR, MICRO-EDGE, .050, VERTICAL, TIN PLATE, METAL LATCH							
	3 PLC ± 4 PLC ± ANGLES	- - ± -	APPLICATION SP	EC	SIZE	CAGE CODE	DRAWING NO					RESTRICTED TO
	FINISH		WEIGHT	_	A1	00779	C- 582	2202	1			
	/3	5\/4\	CUSTOMER	DRAWING				SCALE	1:1	SHEET	0F	1 REV B1

В