

1-1757824-2
Product Details



1-1757824-2
(M24308/2-16)

TE Internal Number: 1-1757824-2


Active


View 3D PDF

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029


Always EU RoHS/ELV Compliant
(Statement of Compliance)

Product Highlights:

- Connector
 - Product Series = 90
 - Connector Style = Receptacle
 - Contact Type = Socket
 - Density = High

[View all Features](#)


Add to My Part List


Request Sample


Find Similar Products


Buy Product

Have a Question?

Chat with a Product Information Specialist



Quick Links

- Check Pricing & Availability
 - Search for Tooling
 - Product Feature Selector
 - Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- [AMPLIMITE RECEPTACLE ASSY,SIZE 1 THRU 6 SERIES 90 WI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:
(CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version B)
 - [3D Model](#) (IGES, Version B)
 - [3D Model](#) (STEP, Version B)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insert Arrangement](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features
(Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
 - [Product Series](#) = 90
 - [Shell Size](#) = 6
 - [Shell Material](#) = Steel
 - [Termination Method to Wire/Cable](#) = Crimp
 - Mounting Hole Diameter (mm [in]) = 3.05 [.120]
 - Comment = Size 22 sockets supplied with receptacles are loose piece.; "F" is stamped on connectors following M24308 part number as required. "F" designates cadmium shell plating.

Body Related Features:

- [Number of Positions](#) = 104
 - [Blindmate](#) = No
 - [Non-Magnetic](#) = No
 - [Rear Grommet](#) = No
 - [Power/Signal/Coax Combination](#) = No
 - [Shell Plating](#) = Zinc
 - Mount Style = Mounting Holes
 - Retention Clip Material = Stainless Steel

Contact Related Features:

- Contact Type = Socket
 - [Contact Size](#) = 22
 - [Contact Style](#) = Crimp Snap-in

Housing Related Features:

- Connector Style = Receptacle

Configuration Related Features:

- [Density](#) = High

Industry Standards:

- Government/Industry Qualification = Yes
 - Government/Industry Part Number = M24308/2-16
 - [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
 - [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
 - RoHS/ELV Compliance History = Always was RoHS compliant
 - NASA Qualification = No

Conditions for Usage:

- Applies To = Wire

Other:

- Brand = AMP


BOOKMARK




Corporate Information

Who We Are

Investors

News Room

Supplier Portal

Careers

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat with Us](#)

[Find a Phone Number](#)


[Search Knowledge Base](#)

[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

