

Products



My Account

About TE

Alternates/Statement of Compliance)





Email

🗓 Share

Quick Links-

Pricing & Availability Search for Tooling

View Mating Products (5) Product Feature Selector

Contact Us About This Product

Support Center

What can we help you find?

🗎 Print

Home > Products > Ribbon Cable Interconnects > Product Feature Selector > Product Details

Resources

# 1-499913-0 Product Details

Industries



1-499913-0

TE Internal Number: 1-499913-0

Active


Product Highlights:


- Header
- Header Type = Universal Ejection Pin Headers

5 of 6 EU RoHS/ELV Compliant (Find RoHS Compliant)

- AMP-LATCH Product Line
- Standard Profile
- 50 Positions

View all Features









Innovation

## Documentation & Additional Information

#### Product Drawings:

HEADER ASSY, UNIVERSAL, AMP-LATCH (PDF, English)

#### Catalog Pages/Data Sheets:

None Available

#### Product Specifications:

• AMP-LATCH and IDC Header Connectors, .100 x .100 Inc... (PDF, English)

#### Application Specifications:

None Available

#### Instruction Sheets:

AMP\* INSTALLATION PROCEDURES FOR AMP-LATCH\* UNIVERSA... (PDF, English)

#### CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version E)
- 3D Model (IGES, Version E)
- 3D Model (STEP, Version E)

List all Documents

# Additional Information:

Product Line Information

### Related Products:

- Tooling
- Mating Products (5)



## Product Features (Please use the Product Drawing for all design activity)

## Product Type Features:

- Connector Type = Header
- Product Line = AMP-LATCH
- Profile = Standard
- PCB Mounting Orientation = Right Angle
- PCB Mount Retention = Without
- Mating Connector Lock = With
- Ejection Latches = With
- Post Size (mm [in]) = 0.64 [.025]
- Shrouded = Yes
- Latch Type = Short
- Mating Connector Lock Type = Latch

# Termination Features:

- Termination Post Length (mm [in]) = 2.79 [0.110]
- Solder Tail Contact Plating = Tin-Lead

# Dimensions:

PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

# Body Features:

Header Type = Universal Ejection Pin Headers

## Contact Features:

- Contact Plating, Mating Area, Material = Gold (15)
- Contact Shape = Square

## Housing Features:

- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]
- Mating Alignment Type = Center, Dual Polarizing Bar, Military
- Housing Style = 4-Sided
- · Mating Alignment = With
- Housing Material = Thermoplastic GF
- UL Flammability Rating = UL 94V-0
- Housing Color = Black

## Configuration Features:

Number of Positions = 50

## Industry Standards:

- RoHS/ELV Compliance = ELV compliant, 5 of 6 Compliant
- Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C

## Conditions for Usage:

Temperature Rating = Standard

## Other:

Brand = AMP

Corporate Information

About TE Investors News Room Supplier Portal Quick Links

Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

Customer Support

Keep Me Informed











Terms & Conditions

Privacy Policy

Careers

Site Map