



Search bar: What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Product Feature Selector > Product Details

1-88859-0 Product Details

Share Print Email



1-88859-0

TE Internal Number: 1-88859-0
Active

View 3D PDF

Flexible Film Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Socket
- 2.54 mm Centerline

View all Features

Quick Links

- Pricing & Availability
- Search for Tooling
- View Mating Products (1)
- View Contacts (47)
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- HOUSING, RECEPTACLE, FFC, .100 CL (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- Connector, Flexible Flat Conductor Cable, .100 Inch ... (PDF, English)

Application Specifications:

- Flexible Flat Cable (FFC) Housings with Contact Cavi... (PDF, English)

Instruction Sheets:

- Extraction Tools 91047-[] (PDF, English)
- Extraction Tool for Flexible Flat Cable (FFC) (PDF, English)
- Extraction Tools (PDF, English)

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version U)
- 3D Model (IGES, Version U)
- 3D Model (STEP, Version U)

Additional Information:

- Product Line Information

Additional Product Images:

- Typical Application, to-Board
- Typical Application, to-Cable

Related Products:

- Tooling
- Mating Products (1)
- Contacts (47)

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- Type of Connector = Standard
- Wire/Cable Type = FFC
- Mating Connector Lock = With
- Mating Connector Lock Type = Detent
- Color = Black
- Flame Retardant = Yes

Mechanical Attachment:

- Panel Mount Retention = Without
- Mounting Ears = Without

Contact Features:

- Contact Type = Socket

Housing Features:

- Connector Style = Receptacle
- Centerline (mm [in]) = 2.54 [0.100]
- Mating Alignment = With
- Housing Material = Thermoplastic - GF
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Number of Positions = 4
- Number of Rows = Single

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = AMP
- Comment = Use Extraction Tool No. 91092-1 for round wire contacts.

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

