

Product Drawings:

2 TAB, FASTON, P.C.BOARD 6.35 [.250] (PDF, English)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files:

? None Available

? <u>Material</u> = Brass

List all Documents

? Product Line Information

Related Products:

? <u>Tooling</u>

| Product Features (Please use the Product Drawing for all design activity) | |
|---|---|
| Product Type Features: | Body Related Features: |
| ? <u>Product Type</u> = Tab | ? <u>Tab Type</u> = Printed Circuit Board |
| [?] <u>Tab Fit (mm [in])</u> = 6.35 x 0.81 [.250 x .032] | ? Stud Hole = Without |

| ? <u>Finish</u> = Tin | Industry Standards: |
|---|---|
| <u>Mount Angle</u> = Straight | ? <u>RoHS/ELV Compliance</u> = RoHS compliant, ELV |
| Insulation Support = Without | compliant |
| PCB Hole Diameter (mm [in]) = 1.40 [0.055] | ? Lead Free Solder Processes = Wave solder appelle to 240°C. Wave solder appelle to 260° |
| PCB Thickness (mm [in]) = 1.57 [0.062] | capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C |
| Electrical Characteristics: <u>Dimple</u> = With | RoHS/ELV Compliance History = Always was RoHS compliant |
| | Packaging Related Features: |
| Termination Related Features: Provide Height (mm [in]) = 14.02 [0.552] | Packaging Method = Strip |
| | Other: |
| | ? Brand = AMP |
| | |

Provide Website Feedback | Contact Customer Support

Home | Customer Support | Suppliers | Site Map | Privacy Policy | Browser Support © 2008 Tyco Electronics Corporation All Rights Reserved