

## 1-440146-2 Product Details

[Live Product Chat](#)



### 1-440146-2

TE Part Number: 1-440146-2

[Active](#)

[Add to Part List](#)

### High Performance Interconnects (HPI)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

#### Product Highlights:

- 1.25 mm Centerline
- Receptacle
- Number of Positions = 12
- Housing Color = White
- Number of Rows = Single

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(8\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [WIRE TO BOARD SOCKET, HOUSING, 1.25 PITCH.](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Metric Interconnect System \(Restricted to Sony Corpo...](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)
- [Mating Products \(8\)](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Receptacle
- [Number of Positions](#) = 12

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 1.25 [0.049]
- [Number of Rows](#) = Single

#### Housing Related Features:

- [Housing Color](#) = White
- Housing Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)