

Products

Industries

Resources

About TE

My Account

Innovation

Support Center


Home > Products > Switches & Knobs > Product Feature Selector > Product Details

1520230-2 Product Details



Product Highlights View All

- Double Pole Single Throw Configuration (Pole-Throw)
- Toggle Length = 20.65 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal



Documents

Please Note:

🏈 Active

Features

Compliance

Use the Product Drawing for all design activity **Electrical Characteristics** UL/CSA 250V Current 20 Rating (A)

1.50

UL/CSA 250V Horse Power Rating (hp)

UL/CSA 125V Horse

Power Rating (hp)

2.00

Termination Features

Termination Type Screw-In Terminal

Toggle Length (mm [in])

Dimensions

20.65 [0.813]

Bushing Length (mm [in])

11.91 [0.469]

Toggle Style Baton

Configuration Features

Configuration (Pole-Double Pole - Single Throw) Throw

Industry Standards

RoHS/ELV Compliance RoHS compliant, ELV compliant

Lead Free Solder Processes 🔞

Not relevant for lead free process

RoHS/ELV Compliance Always was RoHS compliant History

Other

Brand Alcoswitch

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

About TE Investors News Room Supplier Portal

Careers

Terms & Conditions Privacy Policy

Global Accessibility Statement

Ouick Links

Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center **Customer Support**

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

Keep Me Informed











