

 [Live Product Chat](#)



 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Receptacle
- Tab Fit = 2.79 x 0.79 mm
- Board Mount = No
- Receptacle Style = Straight
- Insulation Support

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Receptacle
- Tab Fit (mm [in]) = 2.79 x 0.79 [.110 x .031]
- Receptacle Style = Straight
- Insulation Support = Insulation Support
- Wire/Cable Type = Regular Wire
- Insulation Diameter (mm [in]) = 2.00-3.00 [.079-.118]
- Insertion Force = Normal
- Material = Brass
- Finish = Tin
- Crimp Type = F-Crimp
- CSA Certified = Yes
- Comment = Versions according to DIN 46247, Part 1, all other versions have dimples, which fit IEC and ISO tabs of nominal Size 2.8.; Chamfered

Mechanical Attachment:

- Board Mount = No

Body Related Features:

- Weld Tab = Without
- Wire Range (mm [AWG]) = 0.50-1.00² [20-17]
- UL Rating = Listed

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- For Hermetic Header Tab = No
- Line = Commercial
- Brand = AMP