

175778-3 Product Details

 [Live Product Chat](#)



175778-3

TE Part Number: 175778-3

 [Active](#)

 [Add to Part List](#)

2mm AMP CT

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Connector Type = Blindmate, Crimp
- Mating Type = Receptacle
- Number of Positions = 3
- Number of Rows = 1

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [crimp type receptacle housing \(amp ct connector 2mm ... \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [AMP Common Termination\(CT\), Connector, 2mm Pitch, Cr... \(PDF, English\)](#)

Application Specifications:

- [Crimping AMP 2.0mm Pitch CT Receptacle Contact \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version D1\)](#)
- [3D Model \(IGES, Version D1\)](#)
- [3D Model \(STEP, Version D1\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = Blindmate, Crimp
- [Mating Type](#) = Receptacle
- [Number of Positions](#) = 3
- Wire Termination Type = Crimp

Mechanical Attachment:

- [Panel Attachment](#) = Without

Body Related Features:

- [Number of Rows](#) = 1
- Centerline (mm [in]) = 2.00 [0.079]

Housing Related Features:

- [Housing Material](#) = Nylon
- [Housing Color](#) = Natural
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Wire

Other:

- Brand = AMP

 [Provide Website Feedback](#) | [Need Help?](#)