


2-487769 - 2 Product Details



2-487769 -2

Active


Flexible Film Connectors

Always EU RoHS/ELV Compliant Statement of Compliance

Product Highlights:

- ? Housing
- 2.54 mm Centerline
- ? Connector Type = Slimline
- ? Number of Positions = 24
- ? Number of Rows = Single

View all Features Find Similar **Products**



Documentation & Additional Information

Product Drawings:

? HOUSING, RECEPTACLE, DETENT, POLARIZED, FFC (PDF, English)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files: (CAD Format & Compression Information ? <u>2D Drawing</u> (DXF, Version N) ? <u>3D Model</u> (IGES, Version N) ? <u>3D Model</u> (STEP, Version N)

Additional Information:

? Product Line Information

Additional Product Images:

? Typical Application

Related Products:

- ? <u>Tooling</u>
- ? Mating Products (12)
- ? Contacts (19)

List all Documents

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Product Type = Housing Connector Type = Slimline Number of Positions = 24 Mating Type = Receptacle Mating Connector Lock = With Mating Connector Lock Type = Detent Mating Polarization = Without Mounting Ears = Without Flame Retardant = Yes 	 Housing Related Features: Housing Material = Thermoplastic Housing Flammability Rating = UL 94V -0 Industry Standards: ROHS/ELV Compliance = ROHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process ROHS/ELV Compliance History = Always was ROHS compliant
Mechanical Attachment: Panel Attachment = Without	Conditions for Usage: ? <u>Terminate To</u> = FFC Cable
Body Related Features: ? <u>Centerline (mm [in])</u> = 2.54 [0.100] ? <u>Number of Rows</u> = Single	Other: ? Brand = AMP

