

Product Type Features:

- Product Type = Header
 - Number of Positions = 8

Contact Related Features:

 <u>Contact Mating Area Plating Material</u> = Gold (15)

 <u>Number of Positions</u> = 8 	(15)
 Mount Angle = Vertical 	 Contact Material = Brass
 PCB Retention Feature = No 	
 <u>Surface Mount Compatible</u> = No 	Housing Related Features:
 <u>Board Standoff</u> = Without 	Housing Material = Thermoplastic Glass
	Reinforced
• <u>Mounting Ears</u> = Without	 Housing Flammability Rating = UL 94V-0
 <u>Mating Connector Lock</u> = With 	
 <u>Mating Connector Lock Type</u> = Detent Windows 	Industry Standards:
 Housing Style = 3-Sided 	 <u>RoHS/ELV Compliance</u> = RoHS compliant, ELV
 Profile = Standard 	compliant
	 Lead Free Solder Processes = Wave solder
Mechanical Attachment:	capable to 240°C, Wave solder capable to 260°
 Mating Post Length (mm [in]) = 6.60 [0.260] 	C, Wave solder capable to 265°C
• <u>Panel Attachment</u> = Without	 RoHS/ELV Compliance History = Always was
	RoHS compliant
Termination Related Features:	
 Termination (Solder) Post Length (mm [in]) = 	Conditions for Usago
3.50 [0.138]	 Conditions for Usage: High Temperature Housing = No
0.00 [0.100]	
Body Related Features:	 Operating Temperature (°C) = -55 - +105
 Header Type = Shrouded 	
 <u>Number of Rows</u> = Dual 	Operation/Application:
	 High Speed Serial Data Connector = No
 <u>Centerline, Matrix (mm [in])</u> = 2.54 [.100] 	
 <u>Selectively Loaded</u> = No 	Packaging Related Features:
 <u>Mount Type</u> = PC Board 	 Packaging Quantity = 1,000
	Other:
	 Brand = AMP

Provide Website Feedback | Need Help?

Home | Customer Support | Suppliers | Site Map | Privacy Policy | Browser Support © 2008 Tyco Electronics Corporation All Rights Reserved