

Product Type Features:	Housing Related Features:
 <u>Product Type</u> = Header 	 Housing Material = Polycarbonate
 Mount Angle = Vertical 	 Housing Color = Green
 Keyed = No 	 Housing Flammability Rating = UL 94V-1
 Number of Positions = 8 	
	Industry Standards:
Mechanical Attachment:	 <u>RoHS/ELV Compliance</u> = RoHS compliant, ELV
 Mating Post Length (mm [in]) = 10.00 [0.394] 	compliant
	 Lead Free Solder Processes = Wave solder
Termination Related Features:	capable to 240°C, Wave solder capable to 260°
 Termination End Plating = Tin (150) 	C, Wave solder capable to 265°C
	 RoHS/ELV Compliance History = Always was RoHS compliant
Body Related Features:	
 Number of Rows = Single 	Conditions for Lleago
 Centerline (mm [in]) = 3.96 [0.156] 	 Conditions for Usage: Terminate To = Printed Circuit Board
	• Ferninate Fo = Frinted Circuit Doard
Contact Related Features:	Packaging Related Features:
 Contact Mating Area Plating Material = Tin 	 Packaging Method = Box
(150)	• Fackaging Method = box
 Contact Material = Phosphor Bronze 	Other:
	Brand = AMP

Provide Website Feedback | Need Help?

Home | Customer Support | Suppliers | Site Map | Privacy Policy | Browser Support © 2008 Tyco Electronics Corporation All Rights Reserved