


### 3-1761711 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**3-1761711 -1**

✓ [Active](#)

#### Pin and Pinless Headers (AMP) - LATCH

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

##### Product Highlights:

- ? Connector Type = Pin Headers
- ? Low Profile
- ? Number of Positions = 34
- ? 2.54 x 2.54 mm Centerline, Matrix
- ? PCB Mount Angle = Vertical

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(10\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- ? [HEADER ASSEMBLY, LONG EJECT LATCH, VERTICAL, LOW PRO...](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- ? None Available

##### Product Specifications:

- ? None Available

##### Application Specifications:

- ? None Available

##### Instruction Sheets:

- ? None Available

##### CAD Files:

- ? None Available

##### Additional Information:

- ? [Product Line Information](#)

##### Related Products:

- ? [Tooling](#)
- ? [Mating Products \(10\)](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- ? Connector Type = Pin Headers
- ? [Profile](#) = Low
- ? [Number of Positions](#) = 34
- ? [PCB Mount Angle](#) = Vertical
- ? [PCB Retention Feature](#) = No
- ? [Mating Polarization Method](#) = Center, Military
- ? [Mating Connector Lock](#) = With
- ? [Housing Style](#) = 4 -Sided
- ? [Ejection Latches](#) = With
- ? Post Size (mm [in]) = 0.64 [.025]
- ? Shrouded = Yes
- ? Mating Polarization = With
- ? Latch Type = Long

##### Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 4.11 [0.162]
- ? Solder Tail Contact Plating = Tin over Nickel

##### Body Related Features:

- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]

##### Contact Related Features:

- ? [Contact Mating Area Plating](#) = Gold Flash over Palladium Nickel
- ? Contact Shape = Square
- ? Contact Material = Phosphor Bronze

##### Housing Related Features:

- ? Housing Material = PBT
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Color = Blue

##### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

##### Conditions for Usage:

- ? [Temperature Rating](#) = Standard

##### Other:

- ? Brand = AMP