

324448 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



324448

✔ [Active](#)

AMPOWER Splices

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Splice Type = Parallel
- ? Wire Size (AWG/CM) = 300,000 CM
- ? Barrel Length = Standard
- ? Barrel I.D. Min. = 19.51 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [WIRE SPLICE, PARALLEL, AMPOWER, WIRE SIZE:300 MCM](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Splice Type = Parallel
- ? Finish = Tin
- ? Material = Copper (Annealed) per ASTM B -75
- ? Comment = Tin Plate per ASTM B -545

Body Related Features:

- ? [Wire Size \(AWG/CM\)](#) = 300,000 CM
- ? [Barrel Length](#) = Standard
- ? [Barrel I.D. Min. \(mm \[in\]\)](#) = 19.51 [0.768]
- ? Wire Range (CMA) = 275,000 - 325,000

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP