

440129-3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



440129-3

✓ [Active](#)

High Performance Interconnects (HPI)

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 2.00 mm Centerline
- Receptacle
- Number of Positions = 3
- Housing Color = Natural
- Number of Rows = Single

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(19\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [2.0MM PITCH HPI, CRIMP HOUSING.](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Metric Interconnect System \(Restricted to Sony Corpo...](#) (PDF, English)
- [AMP 2.0MM PITCH HPI WIRE-TO-BOARD SYSTEM.](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)
- [Mating Products \(19\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Receptacle
- [Number of Positions](#) = 3

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.00 [0.079]
- [Number of Rows](#) = Single

Housing Related Features:

- [Housing Color](#) = Natural
- Housing Flammability Rating = UL 94V-0
- Housing Material = Nylon 66

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP