

5148059 -5 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5148059 -5

Active

Eurocard Type C

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- ? Type C Connectors
- ? Receptacle
- ? Number of Positions = 96
- ? Rows Loaded = A, B, C
- ? Terminate To Printed Circuit Board

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [ASSEMBLY, RECEPTACLE, EUROCARD, TYPE C 96 POSITION, ...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Eurocard Connectors Types B,C,M,Q,R, & Enhanced Typ...](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version O)
- ? [3D Model](#) (IGES, Version O)
- ? [3D Model](#) (STEP, Version O)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Type C Connectors
- ? [Gender](#) = Receptacle
- ? [Number of Positions](#) = 96
- ? [PCB Retention Feature](#) = Yes
- ? [PCB Mount Angle](#) = Vertical
- ? [PCB Thickness \(Minimum\) \(mm \[in\]\)](#) = 1.57 [0.062]
- ? [Post Type](#) = Compliant Post
- ? [Size](#) = Standard
- ? [Make First / Break Last](#) = No
- ? [Bus Type](#) = FUTUREBUS, MULTIBUS (II), NUBUS, VMEbus, VXIBus
- ? [DIN Level](#) = II
- ? [Mounting Ears](#) = With
- ? Toolless (Flat Rock) = Yes
- ? Color = Gray
- ? Comment = Seating tool required.

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 17.00 [0.669]

Body Related Features:

- ? [Rows Loaded](#) = A, B, C
- ? [PCB Retention Method](#) = ACTION (Compliant) Press-fit Posts
- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.64 [.025] Sq.

Contact Related Features:

- ? Contact Material = Copper Alloy

Housing Related Features:

- ? Housing Material = Polymer
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? [Flux-Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board
- ? [High Temperature Housing](#) = No

Other:

- ? Brand = Tyco Electronics