

## 5148468 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**5148468 -1**

TE Part Number: 5148468 -1

**Active**

[Add to Part List](#)

### Eurocard Type C

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Type C Connectors
- ? Plug
- ? Number of Positions = 144
- ? Rows Loaded = A, B, C
- ? Terminate To Printed Circuit Board

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [ASSEMBLY, PIN, EUROCARD, TYPE C, 144/150 POSITION, S...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [Eurocard Connectors Types B,C,M,Q,R, & Enhanced Typ...](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Type C Connectors
- ? [Gender](#) = Plug
- ? [Number of Positions](#) = 144
- ? [PCB Retention Feature](#) = No
- ? [PCB Mount Angle](#) = Right Angle
- ? [Post Type](#) = Solder Post
- ? [Size](#) = Standard
- ? [Make First / Break Last](#) = No
- ? [DIN Level](#) = II
- ? [Mounting Ears](#) = With
- ? Guides = Without
- ? Toolless (Flat Rock) = No
- ? Color = Gray
- ? Comment = Selectively Loaded

#### Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 2.65 [0.104]

#### Body Related Features:

- ? [Rows Loaded](#) = A, B, C
- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.64 [.025] Sq.
- ? Positions Loaded = 1 -40, 43 -50

#### Contact Related Features:

- ? Contact Material = Brass

#### Housing Related Features:

- ? Housing Material = Polyester GF
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? [Flux - Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board
- ? [High Temperature Housing](#) = No

#### Other:

- ? Brand = AMP