

826632-2 Product Details

[Live Product Chat](#)



826632-2

TE Part Number: 826632-2

[Active](#)

[Add to Part List](#)

.100 inch AMPMODU Headers

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Header
- Header Type = Breakaway
- Number of Rows = Dual
- Number of Positions = 4
- Mating Post Length = 6.70 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [AMPMODU II STIFTLISTE ZWEIREIHIG \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version 01\)](#)
- [3D Model \(IGES, Version 01\)](#)
- [3D Model \(STEP, Version 01\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Header
- [Number of Positions](#) = 4
- [Mount Angle](#) = Vertical
- [PCB Retention Feature](#) = No
- [Surface Mount Compatible](#) = No
- [Board Standoff](#) = Without
- [Mounting Ears](#) = Without
- [Mating Connector Lock](#) = Without
- Profile = Standard

Mechanical Attachment:

- [Mating Post Length \(mm \[in\]\)](#) = 6.70 [0.264]
- [Panel Attachment](#) = Without

Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.20 [0.126]
- Solder Tail Contact Plating = Tin

Body Related Features:

- [Header Type](#) = Breakaway
- [Number of Rows](#) = Dual
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]
- [Selectively Loaded](#) = No
- [Mount Type](#) = PC Board

Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (30)
- Contact Material = Phosphor Bronze

Housing Related Features:

- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [High Temperature Housing](#) = No

Operation/Application:

- [High Speed Serial Data Connector](#) = No

Packaging Related Features:

- Packaging Quantity = 1,500

Other:

- Brand = AMP