

## 826925-5 Product Details

[Live Product Chat](#)



### 826925-5

TE Part Number: 826925-5

Active

[Add to Part List](#)

### .100 inch AMPMODU Headers

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Header
- Header Type = Breakaway
- Number of Rows = Dual
- Number of Positions = 10
- Mating Post Length = 6.70 mm

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

### Documentation & Additional Information

#### Product Drawings:

- [AMPMODU II STIFTLISTE ZWEIREIHIG \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version 0\)](#)
- [3D Model \(IGES, Version 0\)](#)
- [3D Model \(STEP, Version 0\)](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Header
- [Number of Positions](#) = 10
- [Mount Angle](#) = Vertical
- [PCB Retention Feature](#) = No
- [Surface Mount Compatible](#) = No
- [Board Standoff](#) = Without
- [Mounting Ears](#) = Without
- [Mating Connector Lock](#) = Without
- Profile = Standard

#### Mechanical Attachment:

- [Mating Post Length \(mm \[in\]\)](#) = 6.70 [0.264]
- [Panel Attachment](#) = Without

#### Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.20 [0.126]
- Solder Tail Contact Plating = Tin

#### Body Related Features:

- [Header Type](#) = Breakaway
- [Number of Rows](#) = Dual
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]
- [Selectively Loaded](#) = No
- [Mount Type](#) = PC Board

#### Contact Related Features:

- [Contact Mating Area Plating Material](#) = Tin over Nickel
- Contact Material = Brass

#### Housing Related Features:

- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [High Temperature Housing](#) = No

#### Operation/Application:

- [High Speed Serial Data Connector](#) = No

#### Other:

- Brand = AMP