


## Product Details for QC20 - BU



**QC20 - BU**

Tyco Part Number: 6 - 1437402 - 3

[Active](#)

### Accessories (Terminal Block)

[RoHS Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- ? Accessory Type = Quick Connect Tab
- ? Tri -Barrier Block Series
- ? Used With JC6, Used With SSB6, Used With SSB7
- ? 8.26 mm Centerline
- ? Block or Strip Style = Barrier Strips

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [QUICK CONNECT TABS .250 WIDE X .032 THICK](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Accessory Type](#) = Quick Connect Tab
- ? [Block or Strip Style](#) = Barrier Strips
- ? [Tab Fit \(mm \[in\]\)](#) = 4.75 x 0.51 [.187 x .020]

#### Mechanical Attachment:

- ? Stackable = Yes

#### Electrical Characteristics:

- ? [Tab Angle](#) = 180°
- ? Tab Material = Brass

#### Body Related Features:

- ? [Block Series](#) = Tri -Barrier
- ? [Used With](#) = JC6, SSB6, SSB7
- ? [Centerline \(mm \[in\]\)](#) = 8.26 [0.325]

#### Contact Related Features:

- ? [Quick Connect Tab Type](#) = Double -Side
- ? Tab Plating = Tin

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- ? Brand = Buchanan