



MSPM101C104 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Pushbutton Switches

MSPM101C104

MSPM101C104 ✔

TE Internal Number: 1825538-3

Product Highlights [View All](#)

- Switch
- Not Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 1.0 VA optimum [100mA max., 50 VDC max.]
- Process Sealed

[Pricing & Availability](#) ▶

[Request Sample](#) ▶

[Add to My Part List](#) +

[Buy Product through Distributor](#) ▶

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features

| | |
|----------------|----------------|
| Product Type | Switch |
| Mount Angle | Vertical |
| Actuator Style | Cap - Supplied |

Electrical Characteristics

| | |
|----------------|--|
| Contact Rating | 1.0 VA optimum [100mA max., 50 VDC max.] |
|----------------|--|

Termination Features

| | |
|------------------|-----------|
| Termination Type | Wire Lugs |
|------------------|-----------|

Dimensions

| | |
|---------------------------|--------------|
| Actuator Length (mm [in]) | 8.02 [0.316] |
| Bushing Diameter | 1/4-40 |

Body Features

| | |
|-------------------|-----------|
| Mount Style | Panel |
| Actuator Profile | Extended |
| Bushing Style | Threaded |
| Case Material | Steel |
| Actuator Material | Polyamide |

Contact Features

| | |
|-----------------|------------------|
| Contact Plating | Gold over Nickel |
|-----------------|------------------|

Housing Features

| | |
|----------------|-----|
| Process Sealed | Yes |
| Low Profile | No |

Configuration Features

| | |
|----------------------------|----------------------------|
| Tactile | No |
| Configuration (Pole-Throw) | Single Pole - Single Throw |
| Operating Function | Normally Open, Momentary |
| Ganged | No |
| ESD Grounding Terminal | Without |
| Number of Actuators | Single |
| Illuminated | No |
| Dust Proof | No |
| Support Bracket | Without |
| Snap Action | Without |
| Detent Style | Soft |

Industry Standards

| | |
|-----------------------------|---------------------------------------|
| RoHS/ELV Compliance | RoHS compliant, ELV compliant |
| Lead Free Solder Processes | Hand solderable with lead free solder |
| RoHS/ELV Compliance History | Always was RoHS compliant |

Conditions for Usage

| | |
|--------------------|----------|
| Temperature Rating | Standard |
|--------------------|----------|

Operation/Application

| | |
|-------------------------|---------------------------------|
| Actuator Force (g [oz]) | 113.40 - 198.50 [4.000 - 7.000] |
|-------------------------|---------------------------------|

Packaging Features

| | |
|------------------|-------------|
| Packaging Method | Loose Piece |
|------------------|-------------|

Other

| | |
|---------|-------------------|
| Series | MSPM |
| Brand | Alcoswitch |
| Comment | Red cap supplied. |

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

