



Thermal Transfer Printable Labels- # THT-17-423-3

SIZE: 2.000" W x 1.000" H (50.800 mm W x 25.400 mm H)
MATERIAL: Permanent Polyester
QTY/UOM: 3,000/Roll
CATALOG #: THT-17-423-3
PRODUCT #: 30131

\$129.53 MSRP (\$US)

QTY:

[OVERVIEW](#) | [SPECIFICATIONS](#)

Description for Thermal Transfer Printable Labels

BradyBondz™ polyester labels for thermal transfer printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of Thermal Transfer Printable Labels

Application(s): Bottles, Conical Tube, Deep Well Plate, General & Industrial Identification, General Identification, Laboratory Identification, Petri Dish, Through Hole- Top
Agency Approval (s)/Compliance: AGA Approved, CSA Approved, HalogenFree (DIN VDE 0472/parts 815), UL Recognized
Size: 2.000" W x 1.000" H (50.800 mm W x 25.400 mm H)
Printable Area: 2.000" W x 1.000" H (50.800 mm W x 25.400 mm H)
Web Width: 2.200" (55.88 mm)
Label Type/Style: Label
Vertical Repeat: 1.125" (28.58 mm)
Color: White
Finish: Gloss
Qty Per Row: 1
Material Type: Polyester
Material Description: Permanent Polyester
Brady Material #: B-423
General ID Catalog: [pg. 88](#)
Recommended Ribbon Series: 6000
Suggested Ribbon Part#: R6000
Acceptable Ribbon Series: 4900, 6200
After Process: Yes, this material will work with this application
Environment: Autoclave, Freezer
Printer Compatibility: BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 360X Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers
Surface: Smooth
Surface Mount Technology: No, this material does not work with this application
Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
RoHS Compatibility: Compliant with RoHS DirectiveNOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.
QTY/UOM: 3,000/Roll

[Customer & Tech Support](#)
[Find a Distributor](#)
[Submit Product Feedback](#)
[Submit Website Feedback](#)
[Contact Us](#)
[Site Map](#)

[Distribution Partners](#)
[Bradyserve.com](#)
[BradyDistributor.com](#)
[Minimum Advertised Price Policy](#)

[Corporate Info](#)
[About Brady](#)
[Bradycorp.com](#)
[Privacy Policy](#)
[Legal Information](#)
[ISO Certified](#)
[Terms of Use](#)
[Terms and Conditions of Sale](#)

[Brady International Sites](#)
[Canada](#) | [Brazil](#) | [Europe, Africa, Middle East](#)
[Canada \(Français\)](#) | [Asia](#)
[Latin America](#) | [Australia](#)