# HARDWARE

701-7326

# **MACHINE SCREWS, ROUND HEAD**

STEEL, PLATED 2-56 x 1/4

701-7002 2-56 x 1/2 701-7004 2-56 x 3/4 701-7006



3-48 X 3/4	701-7010
4-40 x 1/4	701-7015
4-40 x 3/8	701-7016
4-40 x 1/2	701-7017
4-40 x 5/8	701-7018
4-40 x 3/4	701-7019

6-32 x 1/4	701-7024
6-32 x 3/8	701-7025
6-32 x 1/2	701-7026
6-32 x 5/8	701-7027
6-32 x 3/4	701-7028
6-32 x 1	701-7029
8-32 x 1/4	701-7035
8-32 x 3/8	701-7036

8-32 x 1/2

8-32 x 5/8

701-7039	
701-7045	
701-7046	
701-7047	
701-7048	

701-7037

701-7038

# **MACHINE SCREWS, ROUND HEAD**

BRASS, PLATED

4-40 x 1/4	701-7215
4-40 x 3/8	701-7216
4-40 x 1/2	701-7217
6-32 x 1/4	701-7224
6-32 x 3/8	701-7225
6-32 x 1/2	701-7226
8-32 x 1/4	701-7235
8-32 x 3/8	701-7236

# **MACHINE SCREWS, BINDING HEAD**

701-7237

701-7115

8-32 x 1/2

STEEL, PLATED

2-56 x 1/4	701-7102
2-56 x 1/2	701-7104
2-56 x 5/8	701-7105
3-48 x 1/4	701-7110



701-7117 701-7119 4-40 x 3/4 6-32 x 1/8 701-7122 701-7123 6-32 x 3/16 701-7124 6-32 x 1/4 701-7125 6-32 x 3/8 701-7126 6-32 x 1/2 6-32 x 5/8 701-7127 701-7128 6-32 x 3/4

8-32 x 1/4 701-7135 8-32 x 5/16 701-7136 701-7137 8-32 x 3/8 701-7138 8-32 x 1/2 8-32 x 3/4 701-7139

701-7145 10-32 x 1/2 701-7147 10-32 x 3/4

### **MACHINE SCREWS, OVAL HEAD RACK** SCREW STEEL PLATED



Marie Committee of the	
6-32 x 3/4	701-7178
8-32 x 3/4	701-7188
10-32 x 1/2	701-7196
10.22 v 2//	701-7109

# **COUNTER SUNK WASHERS**

STEEL, NICKEL PLATED



NO.6 701-7796 NO.8 701-7798 NO.10 701-7799

#### **HEXAGON NUTS**

10-32 x 3/8 x 1/8

BRASS, PLATED 2-56 x 3/16 x 1/16 701-7312 3-48 x 3/16 x 1/16 701-7315 4-40 x 1/4 x 3/32 701-7317 6-32 x 1/4 x 3/32 701-7319 701-7320 6-32 x 5/16 x 7/64 8-32 x 1/4 x 3/32 701-7322 8-32 x 5/16 x 7/64 701-7324 8-32 x 11/32 x 1/8 701-7323 701-7325 10-32 x 5/16 x7/64



## **VOLUME CONTROL-SWITCH** AND POTENTIOMETER NUTS

HEX BRASS, NICKEL PLATED

1/4-20 x 7/16 x 3/16	701-7410
1/4-28 x 3/8 x 3/32	701-7411
1/4-28 x 3/8 x 1/8	701-7412
1/4-32 x 5/16 x 5/64	701-7413
1/4-32 x 11/32 x 3/32	701-7414
1/4-32 x 3/8 x 3/32	701-7415
5/16-32 x 7/16 x .101	701-7420
5/16-32 x 3/8 x 3/32	701-7421
3/8-32 x 1/2 x 3/32	701-7425
*3/8-32 x 1/2 x 3/32	701-7426
3/8-32 x 9/16 x 3/32	701-7427
15/32-32 x 9/16 x 5/64	701-7430
15/32-32 x 9/16 x 3/32	701-7432
*Steel Plated	

#### RING NUTS

BRASS, NICKEL PLATED

'01-7440
701-7441

#### HEXAGON

STEEL NUTS

2-56 x 3/16 x 1/16	701-7352
3-48 x 3/16 x 1/16	701-7355
4-40 x 1/4 x 3/32	701-7357
6-32 x 1/4 x 3/32	701-7359
6-32 x 5/16 x 7/64	701-7360
8-32 x 5/16 x 7/64	701-7364
10-32 x 3/8 x 1/8	701-7365
1/4-20 x 7/16 x 3/16	701-7370



#### **NYLON SCREWS**

BINDING HEAD



701-6515	6-32 x 5/8	701-6528
701-6516	6-32 x 3/4	701-6529
701-6517	8-32 x 1/4	701-6544
701-6525	8-32 x 3/8	701-6545
701-6526	8-32 x 1/2	701-6546
701-6527	8-32 x 5/8	701-6547
	701-6516 701-6517 701-6525 701-6526	701-6516 6-32 x 3/4 701-6517 8-32 x 1/4 701-6525 8-32 x 3/8 701-6526 8-32 x 1/2

#### **NYLON SCREWS**

OUND HEAD	

4-40 x 1/4	701-6615	6-32 x 5/8	701-6628
4-40 x 3/8	701-6616	6-32 x 3/4	701-6629
4-40 x 1/2	701-6617	8-32 x 1/4	701-6644
6-32 x 1/4	701-6625	8-32 x 3/8	701-6645
6-32 x 3/8	701-6626	8-32 x 1/2	701-6646
6-32 x 1/2	701-6627	8-32 x 5/8	701-6647

#### **NYLON SCREWS**

FLAT HEAD



4-40 x 1/4	701-6715	6-32 x 5/8	701-6728
4-40 x 3/8	701-6716	6-32 x 3/4	701-6729
4-40 x 1/2	701-6717	8-32 x 1/4	701-6744
6-32 x 1/4	701-6725	8-32 x 3/8	701-6745
6-32 x 3/8	701-6726	8-32 x 1/2	701-6746
6-32 x 1/2	701-6727	8-32 x 5/8	701-6747

#### NYLON NUTS. HEXAGON

701-7570 4-40 x 1/4 6-32 x 5/16 701-7572 701-7574 8-32 x 11/32 10-32 x 3/8 701-7576



#### **KNURLED THUMB NUTS**

BRASS NICKEL PLATED

DIO 100, HIOILE	P1 44 PP PP
6-32 x 3/8 x 1/4	701-7601
8-32 x 7/16 x 5/16	701-7602
10-24 x 1/2 x 21/64	701-7603
10-32 x 1/2 x 21/64	701-7604
1/4-20 x 5/8 x 3/8	701-7605



#### **BATTERY NUTS**

BRASS, NICKEL PLATED

6-32	X	11/32	х	13/64	701-7606
8-32	х	11/32	Х	13/64	701-7608



## **LOCKWASHERS, INTERNUL TOOTH**

STEEL, PLATED

O.D.	THK.	
3/16	.010	701-7702
7/32	.012	701-7703
1/4	.015	701-7704
9/32	.018	701-7706
11/32	.020	701-7708
3/8	.022	701-7710
15/32	.026	701-7714
11/16	.032	701-7718
1/2	.018	701-7719
19/32	.020	701-7720
	3/16 7/32 1/4 9/32 11/32 3/8 15/32 11/16 1/2	3/16 .010 7/32 .012 1/4 .015 9/32 .018 11/32 .020 3/8 .022 15/32 .026 11/16 .032 1/2 .018

### **LOCKWASHERS, EXTERNAL TOOTH**

STEEL, PLATED

I.D.			1	
CLEAR	O.D.	THK.	7	M
NO.4	1/4	.015	701-7724	
NO.6	5/16	.018	701-7726	
NO.8	3/8	.020	701-7728	
NO.10	13/32	.022	701-7730	
1/4	1/2	.026	701-7734	
3/8	11/16	.032	701-7738	

### (SPLIT) LOCKWASHERS

STEEL PLATED

I.D. CLEAR	
NO.4	701-7774
NO.6	701-7776
NO.10	701-7781
1/4	701-7782
5/16	701-7783



#### **FLAT WASHERS**

STEEL DI ATED

OILLL, I	LAILD		
I.D.			
CLEAR	O.D.	THK.	
NO.2	1/4	1/32	701-7742
NO.4	5/16	1/32	701-7744
NO.6	3/8	1/32	701-7746
NO.8	3/8	1/32	701-7748
NO.10	3/8	1/32	701-7750
1/4	9/16	3/64	701-7754
2/9	5/8	1/32	701-7758

- · MINIATURE DIAMETERS ON REQUEST.
- PRICES ON BULK QUANTITIES AVAILABLE ON REQUEST
- · AVAILABLE IN BRASS, STAINLESS STEEL AND ALL FINISHES.
- AVAILABLE IN ALL HEAD STYLES, BOTH SLOTTED AND PHILLIPS.



e-mail: info@concord-elex.com 800-847-4162 (outside N.Y.S.) 212-777-6571 · fax. 212-995-0161