


2110QA, 2111QA, 2112QA, 2113QA Series Non-Relampable Neon Indicator Lights

Description and Features



Mounting: Ø.310 MIN., supplied with push-on speednut SN1287.
Terminals: Quick-connect, tinned brass, .187 x .020
Lens: Polycarbonate
Bezel: White nylon.
Housing: White Nylon

	Neon	
Lens Color	Model No.	Model No.
	(105-125VAC)	(208-250VAC)
Red	2110QA1	2111QA1
Clear	2110QA2	-
Amber	2110QA3	-
White	2110QA4	2111QA4
Green	2112QA5*	2113QA5*
Lamp	C2A+Resistor	C2A+Resistor

* Incorporates G2B lamp and resistor. Underwriters Laboratories (UL) File No. E20356

