

REV. 6 DCO 102710

COIL: @ 25°C	CUSTOMER DATA SHEET
RESISTANCE 300 OHM\$ ±10% NOMINAL VOLTAGE 26.5 VDC MUST OPERATE 13.0 VDC	BLUE BEAD A2 XI B3 X2 B2 A1
MUST RELEASE 2.3 VDC ENVIRONMENT:	B36 X26 GAI TERMINAL VIEW
VIBRATION 10 CPS TO 2000 CPS @ 20 g's SHOCK 50 g's 11 MS. DURATION TEMPERATURE -65 °C TO +125 °C	CONTACT RATING: 10 AMPS 28 VOC 5 AMPS 115 VAC/400 Hz RESISTIVE 50.000 OPERATIONS
NOTES: OPERATE & RELEASE 15 MS MAX. OPERATE BOUNCE 5 MS MAX.	DR. BSH 8/17/01 CK. TLG 8-17-01
RELEASE BOUNCE 5 MS MAX.	CII Technologies advanced control electronic solutions
CUST. NO. M5757/23-002 REV. "07" RELAY	B07D992BZ2-0050
F-718 REV. 3	<u> </u>