


FCA - 210 - 1026M Product Details



Military/Aerospace Mid - Range Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? FCA 10-25 Amp Relay Series
- ? DC Actuating System
- ? Coil Voltage = 28 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Current Rating = 10 Amps.

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

FCA-210 - 1026M
(M83536/10 - 026M)
✔ [Active](#)

Documentation & Additional Information

Product Drawings:

- ? [MSD RELAY](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Terminal Type](#) = Solder Hook

Electrical Characteristics:

- ? [Actuating System](#) = DC
- ? [Coil Voltage \(VDC\)](#) = 28
- ? [Current Rating \(Amps.\)](#) = 10

Termination Related Features:

- ? [Terminal Plating](#) = Tin -Lead
- ? Auxiliary Contacts = Without

Body Related Features:

- ? Series = FCA 10 -25 Amp Relay
- ? [Mount Type](#) = Side Mount

Configuration Related Features:

- ? [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- ? [Coil Suppression Diode](#) = With
- ? Coil Magnetic System = Polarized, Monostable

Industry Standards:

- ? Government/Industry Qualification = No
- ? Government/Industry Part Number = M83536/10 -026M
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

Other:

- ? Brand = CII