

[Products](#)[Industries](#)[Resources](#)[About TE](#)[My Account](#)[Innovation](#)[Support Center](#)

[Home](#) > [Products](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

B07D034BB2-0120 Product Details

[Share](#)[Print](#)[Email](#)

 **Active**

Military/Aerospace High Performance Relays

B07D034BB2-0120 = M5757/23-010

B07D034BB2-0120

TE Internal Number: 1617004-9

Product Highlights [View All](#)

- 07 Full Size Relay Series
- Input Voltage = 12 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 10 A
- Non Polarized, Monostable Coil - Magnetic System

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Feedback](#)[Documents](#)[Features](#)[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

MOSFET Driver Without

Mechanical Attachment

Mounting Options PC Board

Electrical Characteristics

Input Voltage (VDC) 12

Contact - Rated Current (A) 10

Coil Suppression Diode Without

Coil Polarity Protection Diode Without

Coil - Resistance (Ω) 75

Coil Power Measurement Milliwatts

Coil - Rated Power, DC (mW) 1920

Actuating System DC

Shock 100G's, 6ms

Vibration 20G's, 10 to 2000Hz

Termination Features

Termination Type PC Pins

Body Features

Enclosure Type Hermetically Sealed

Configuration Features

Contact - Arrangement 2 Form C, DPDT, 2 C/O

Coil - Magnetic System Non Polarized, Monostable

Transistor Driver Without

Industry Standards

Government/Industry Qualification Yes

Government/Industry Part Number M5757/23-010

RoHS/ELV Compliance Not ELV/RoHS compliant

Lead Free Solder Processes Not relevant for lead free process

Approved Standards M5757 Qualified

Conditions for Usage

Temperature Range (°C) -65 - +125

Other

Series 07 Full Size Relay

Brand CII

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

