




MICROSMD150F-2 Product Details

[Share](#) | [Print](#) | [Email](#)


MICROSMD150F-2

TE Internal Number: RF1437-000

[Active](#)

PolySwitch Resettable Devices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Vmax = 6 V
- Imax = 40 A
- Family Name = microSMD
- Surface Mount Construction

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT](#) (PDF, English)

Product Specifications:

- [microSMD150F](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL File Number = E74889
- CSA File Number = CA78165

Electrical Characteristics:

- Vmax (V) = 6
- Imax (A) = 40
- [IH \(Room Temperature\) \(A\)](#) = 1.5
- [IT \(Room Temperature\) \(A\)](#) = 3.00
- [Rmin \(Ω\)](#) = 0.04
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.11

Termination Features:

- Construction = Surface Mount

Contact Features:

- [Family Name](#) = microSMD

Configuration Features:

- [Form Factor \(inches\)](#) = 1210
- [Form Factor \(mm\)](#) = 3225

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72111045

Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

