## Dialight

557 Series High Intensity LED Panel Mount Indicators for <sup>11</sup>/<sub>16"</sub> Mounting Hole Watertight



## **FEATURES / BENEFITS**

- Daylight viewability
- ▲ Tamperproof /Designed for high durability
- ▲ Long life, up to 100k hours
- Uniform illumination
- ▲ Low profile flat lens design

## **APPLICATIONS**


The 557 Series LED Panel Mount Indicators incorporate both InGaN and AlInGaP technologies to offer higher intensities. This is a highly durable package, designed to withstand outdoor applications susceptible to rain, dust, and sunlight.

- Instrument panels
- Vending, gaming
- Transportation rail, bus, airline
- ... and many more!

Lane control

## SPECIFICATIONS

- Available in red, yellow, green, blue, and white
- ▲ Voltage range of 5, 12, 24 VDC
- A Housing material: White polycarbonate
- Lens material: Polycarbonate 94 VO
- Watertight seal from front of panel meets MIL-L-3661B Maximum mounting torque - 15 in./lb.
- ▲ Front mounting in <sup>11</sup>/<sub>16"</sub> clearance hole
- Operating temperature: -25°C to +85°C
- ▲ Storage temperature: -30°C to +100°C



#### Dialight reserves the right to make changes at any time in order to supply the best product possible.

Please see back of page for part numbers and additional specifications.



**Dialight Corporation** 

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

a Roxboro Group Company

MDEL557U001\_B

# Dialight

557 Series High Intensity LED Panel Mount Indicators for <sup>11</sup>/<sub>16"</sub> Mounting Hole Watertight

PART NUMBER	COLOR	VOLTAGE (VDC)	CURRENT (mA)	TYPICAL INTENSITY (fL)
557-1502-203	Red	5	80	1000
557-1602-203	Green	5	16	1000
557-1702-203	Yellow	5	80	1000
557-1802-203	Blue	5	16	250
557-1002-203	White	5	16	700
557-1503-203	Red	12	20	1000
557-1603-203	Green	12	16	1000
557-1703-203	Yellow	12	20	1000
557-1803-203	Blue	12	16	250
557-1003-203	White	12	16	700
557-1505-203	Red	24	20	1000
557-1605-203	Green	24	16	1000
557-1705-203	Yellow	24	20	1000
557-1805-203	Blue	24	16	250
557-1005-203	White	24	16	700

## **LED Panel Mount Indicator Selection**

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options. Please visit our website for more information.

### www.dialight.com

- ▶ .156" **558 Series**
- ▶ .250" *559 Series*
- ▶ 5mm *605 Series*
- ▶ 6mm 606 Series
- ▶ 7mm 607 Series

- ▶ 8mm 608 Series
- ▶ 9mm *609 Series*
- ▶ 10mm 610 Series
- ▶ 11/16" Watertight 557 Series
- ▶ 1" Watertight *556 Series*

Custom capabilities: Please contact factory regarding customizing these indicators to your specific requirement.

Dialight reserves the right to make changes at any time in order to supply the best product possible.



**Dialight Corporation** 

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

a Roxboro Group Company

MDEL557U001\_B